

#### Assignment of connections and functions:

E1: venting mini-measuring connection, MA.1.ST see sheet-no.1650

E2: drainage of filter, dirt side E3: drainage of filter, clean side

M1: measure connection in the housing cover, dirt side

FILTER UNIT, mobile Series UM 80 **PN 4**  Sheet No. 4015 J

# 1. Type index:

1.1. Filter unit: (ordering example)

UM. 80. 6VG. 10. B. P. -. P04. W06. L01. L05. O 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12

1 series:

UM = filter unit, mobile

2 nominal size: 80

3 | filter-material and filter-fineness:

10 VG = 10  $\mu m_{(c)}$ , 6 VG = 7  $\mu m_{(c)}$ , 3 VG = 5  $\mu m_{(c)}$ , 1 VG = 4 $\mu m_{(c)}$  glass fibre

10 WVG = 10  $\mu$ m<sub>(c)</sub>, 3 WVG = 5  $\mu$ m<sub>(c)</sub> Watersorp-filter element

4 resistance of pressure difference for filter element:

10 =  $\Delta p \ 10 \ bar$ 

5 filter element design:

B = both sides open

6 sealing material:

P = Nitrile (NBR) V = Viton (FPM), by agreement

7 filter element specification:

= standard

VA = stainless steel

IS06 = for HFC application, see sheet-no. 31601

8 pump unit:

P04 = pump unit 04, NG 80.50 (standard-pump unit)

9 motor: (W = alternating current motor)

motor	electrical connection		volume flow	max. viscosity	docno.
W06 1)	230V	50Hz	71,0 l/min	10-400 mm <sup>2</sup> /s	43056-4
W06 1)	230V	60Hz	85,0 l/min	10-400 mm <sup>2</sup> /s	43056-4
W09 <sup>1)</sup>	110V	60Hz	85.0 l/min	10-400 mm <sup>2</sup> /s	43057-4

1) standard-motor

10 suction connection 1 1/2 ": (see sheet-no. 31961-4)

L01 = hose-lance

L02 = hose-fitting-lance

L03 = hose-lance-protective filter

L04 = hose- fitting-lance-protective filter

11 discharge connection 1 1/4 ": (see sheet-no. 31961-4)

L05 = hose-lance

L06 = hose-fitting-lance

L21 = hose-fitting

12 clogging indicator at M1:

= without 0 = visual, 2,5 bar

# **1.2. Filter element:** (ordering example)

01NR. 630. 6VG. 10. B. P. -2 3 4 5 6 7

1 series:

01NR. = standard-return-line filter element according to DIN 24550, T4

2 nominal size: 630

3 - 7 see type index-filter unit

### Notice:

Only operate all motors listed on this data sheet in combination with the pump unit specified on the type plate under item 8.

Changes of measures and design are subject to alteration!



### Friedensstrasse 41, 68804 Altlussheim, Germany

phone +49 - (0)6205 - 2094-0 e-mail filtration@eaton.com +49 - (0)6205 - 2094-40 www.eaton.com/filtration

### 2. Spare parts:

item	designation	qty.	dimension	article-no.
1	filter element	1	01NR. 630	
2	housing cover	1	30600-3	315492
3	mini-measuring connection	1	MA.1.ST	305453
4	screw plug	2	G ½	304678
5	straining screw	1	30595-3	316312
6	O-ring	1	140 x 6	315392 (NBR)
7	electric motor	1	according to type index	
8	pump unit P04	1	NG 80.50	317139
9	clogging indicator (series)	1	visual Ø 40	315452
10	O-ring	1	22 x 3	304387 (NBR)
11	O-ring	2	70 x 4	306253 (NBR)
12	O-ring	2	45 x 3	304991 (NBR)
13	O-ring	1	18 x 3	304359 (NBR)
14	O-ring	1	37,69 x 3,53	304353 (NBR)
15	O-ring	1	47,22 x 3,53	305078 (NBR)
16	suction hose 1 1/2 "	1	according to type index	
17	discharge hose 1 1/4 "	1	according to type index	

## 3. Designation:

The mobile filter unit is intended for oil maintenance on hydraulic systems.

The area of application comprises: - secondary flow filtration in addition to the existing operating filter

- secondary flow filtration without the action of the operating filter

- filtration when filling the oil reservoir.

The filter unit must not be used to pump contaminated hydraulic fluids and is therefore designed without a switchover fitting to bypass the filter. The compact structural design on a base plate without pipe satisfies the prerequisites for small dimensions and high reliability. The transporting trolley makes it possible to move close up to confined locations with difficult access, and to fix the accessories (such as hoses and the connection cable) in a safe and reliable manner.

Oil flowing out of the suction and/or discharge hose or the outflow openings is collected by the filter unit's oil trough, without causing any environmental damage. The suction hose DN 40 and the discharge hose DN 32 are approximately 2700 mm long inclusive of the lance.

The device is equipped with a gear pump driven by an E-motor. The flow conveyed by the geared pump is fed over a filter element to DIN 24550, T4, nominal size 630.

Depending on the customer's wishes, the filter fineness is either 4, 5, 7 or 10 µm<sub>(c)</sub>. The contamination level of the filter element can be read off from a pressure display in the cover of the filter.

At a pressure >2.5 bar (red area of the scale field), the filter element is contaminated and it must be replaced with a new filter ele-

The filter element can be changed without tools. After removing the straining screw and taking off the housing cover, the filter element is accessible and it can be exchanged. The filter elements are supplied complete with seals. Since it is not possible to clean the elements, the user must always keep an adequate supply of spare elements in stock.

To protect against overpressure, the filter unit is fitted with a safety valve. Pressure setting about 4 bar.

The E-motor is made safe with a motor-protection-switch against overloading. At a working pressure > 4 bar, the motor-protectionswitch cuts the E-motor out.

The line, venting and draining connections are identified according to their function. Drainage is necessary when cleaning the filter unit in connection with the change of filter element, and when changing the fluid medium.

#### 4. Technical data:

filter-fineness: 4, 5, 7 or 10 µm<sub>(c)</sub> oil temperature: -5 bis +60°C weiaht: approx, 73 kg

operating medium: hydraulic oil based on mineral oil from 10 mm²/s,

other media on request


Classified under the Pressure Vessel Directive 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. Classified under ATEX Directive 2014/34/EU according to specific application (see questionnaire sheet-no. 34279-4).


EN 4015 J

# 5. Symbols:

filter unit without clogging indicator

filter unit with visual clogging indicator





#### 6. Test methods:

Filter elements are tested according to the following ISO standards:

ISO 2941 Verification of collapse/burst resistance ISO 2942 Verification of fabrication integrity

ISO 2943 Verification of material compatibility with fluids

ISO 3723 Method for end load test

ISO 3724 Verification of flow fatigue characteristics

ISO 3968 Evaluation of pressure drop versus flow characteristics

ISO 16889 Multi-pass method for evaluating filtration performance